



Assembly Instruction for 1100ML TYPE PLUS 45

ALUMINUM BOTTLES U.N. APPROVED AS SINGLE PACKAGINGS (1B1).

This bottle has been tested and approved with the following components:

Option 1 : Group I, II, III

- 1/ ALUMINUM BOTTLE**
- 2/ LDPE PLUG**
- 3/ PP CAP WITH ALPE/PEE LINER**

After filling, insert the sealing plug to full depth by pushing it down, screw the cap to the following recommended torque: 53 Inch per lbs.

Recommended Torque Wrench. Item # TORQ009

Custom chuck. Item # ADAPT45

Option 2 : Group I, II, III

- 1/ ALUMINUM BOTTLE**
- 2/ PP CAP WITH PTFE (Teflon) LINER**

After filling, screw the cap to the following recommended torque: 62 Inch per lbs.

Recommended Torque Wrench. Item # TORQ009

Custom chuck. Item # ADAPT45



Option 3 : Group I, II, III

- 1/ ALUMINUM BOTTLE**
- 2/ PP CAP WITH ALPE/PEE LINER**

After filling, screw the cap to the following recommended torque: 53 Inch per lbs.

Recommended Torque Wrench. Item # TORQ009
Custom chuck. Item # ADAPT45

Labeling and marking are the shipper responsibility.
Elemental Container assumes no responsibility for the package integrity or compliance to the U.N. hazardous goods regulations unless all package components are assembled per the above instructions and supplied by Elemental Container.

Product compatibility with the aluminum is the customer responsibility and must be in accordance with the Packaging instructions of the 49CFR. Container compliance is predicated on a product maximum density of 1.2 (H₂O = 1.0).

UN certificates are available upon request.